

ABUS 145/30



Tootekirjeldus

The ABUS 145 padlock consists of a solid aluminium lock body and a steel shackle. It is suitable for closing bags, suitcases, caskets, lockers and more. We recommend the variants 145/20 to 145/30 if you want to insure low value assets or objects with a low risk of theft. The large 145/40 version is very suitable for securing medium value assets or objects with an average risk of theft. The number code can be individually set with three or four number wheels, depending on the size of the lock. Thanks to their light weight, our combination locks 145 are easy to use at any time, even when on the move.

Technologies:

- Solid aluminium lock body with anodized coating – corrosion resistant
- Spring loaded shackle for a better setting of the opening code
- 145/20 and 145/30: Individually resettable 3-digit code
- 145/40: Individually resettable 4-digit code
- Handy operation without key, low weight
- High value of recognition by intensive colours

TOOTENIMETUS	SOODUS	HIND
Đ•Đ°Đ²ĐµÑ•Đ½Đ¾Đ¹ Đ•Đ°Đ¼Đ¾Đ° c Đ°Đ¾Đ´Đ¾Đ¼ ABUS 145/30 (Đ;Đ,Đ½Đ,Đ¹)		16.10 €
Đ•Đ°Đ²ĐµÑ•Đ½Đ¾Đ¹ Đ•Đ°Đ¼Đ¾Đ° c Đ°Đ¾Đ´Đ¾Đ¼ ABUS 145/30 (Đ;ĐµÑĐµĐ±Ñ€Ñ•Đ½Ñ(Đ¹)		16.10 €

TOOTENIMETUS	SOODUS	HIND
$\text{D} \cdot \text{D}^{\circ} \text{D}^2 \text{D}_{\mu} \tilde{\text{N}} \cdot \text{D}^{1/2} \text{D}^{3/4} \text{D}^1$ $\text{D} \cdot \text{D}^{\circ} \text{D}^{1/4} \text{D}^{3/4} \text{D}^{\circ}$ c $\text{D}^{\circ} \text{D}^{3/4} \text{D}' \text{D}^{3/4} \text{D}^{1/4}$ ABUS 145/30 ($\text{D} - \text{D}_{\mu} \text{D} \gg \text{D}_{\mu} \text{D}^{1/2} \tilde{\text{N}} \langle \text{D}^1 \rangle$)		16.10 €
$\text{D} \cdot \text{D}^{\circ} \text{D}^2 \text{D}_{\mu} \tilde{\text{N}} \cdot \text{D}^{1/2} \text{D}^{3/4} \text{D}^1$ $\text{D} \cdot \text{D}^{\circ} \text{D}^{1/4} \text{D}^{3/4} \text{D}^{\circ}$ c $\text{D}^{\circ} \text{D}^{3/4} \text{D}' \text{D}^{3/4} \text{D}^{1/4}$ ABUS 145/30 ($\text{D} \tilde{\text{Z}} \tilde{\text{N}} \in \text{D}^{\circ} \text{D}^{1/2} \tilde{\text{N}} \langle \text{D} \rangle \parallel \text{D}_{\mu} \text{D}^2 \tilde{\text{N}} \langle \text{D}^1 \rangle$)		16.10 €
$\text{D} \cdot \text{D}^{\circ} \text{D}^2 \text{D}_{\mu} \tilde{\text{N}} \cdot \text{D}^{1/2} \text{D}^{3/4} \text{D}^1$ $\text{D} \cdot \text{D}^{\circ} \text{D}^{1/4} \text{D}^{3/4} \text{D}^{\circ}$ c $\text{D}^{\circ} \text{D}^{3/4} \text{D}' \text{D}^{3/4} \text{D}^{1/4}$ ABUS 145/30 ($\text{D} \tilde{\text{S}} \tilde{\text{N}} \in \text{D}^{\circ} \tilde{\text{N}} \cdot \text{D}^{1/2} \tilde{\text{N}} \langle \text{D}^1 \rangle$)		16.10 €
$\text{D} \cdot \text{D}^{\circ} \text{D}^2 \text{D}_{\mu} \tilde{\text{N}} \cdot \text{D}^{1/2} \text{D}^{3/4} \text{D}^1$ $\text{D} \cdot \text{D}^{\circ} \text{D}^{1/4} \text{D}^{3/4} \text{D}^{\circ}$ c $\text{D}^{\circ} \text{D}^{3/4} \text{D}' \text{D}^{3/4} \text{D}^{1/4}$ ABUS 145/30 ($\text{D} \text{C} \text{D}, \tilde{\text{N}}, \text{D}^{\circ} \text{D}^{1/2}$)		16.10 €
$\text{D} \cdot \text{D}^{\circ} \text{D}^2 \text{D}_{\mu} \tilde{\text{N}} \cdot \text{D}^{1/2} \text{D}^{3/4} \text{D}^1$ $\text{D} \cdot \text{D}^{\circ} \text{D}^{1/4} \text{D}^{3/4} \text{D}^{\circ}$ c $\text{D}^{\circ} \text{D}^{3/4} \text{D}' \text{D}^{3/4} \text{D}^{1/4}$ ABUS 145/30 ($\text{D} \tilde{\text{Y}} \tilde{\text{N}} f \tilde{\text{N}} \in \text{D}_{\epsilon} \tilde{\text{N}} f \tilde{\text{N}} \in \text{D}^{1/2} \tilde{\text{N}} \langle \text{D}^1 \rangle$)		16.10 €
$\text{D} \cdot \text{D}^{\circ} \text{D}^2 \text{D}_{\mu} \tilde{\text{N}} \cdot \text{D}^{1/2} \text{D}^{3/4} \text{D}^1$ $\text{D} \cdot \text{D}^{\circ} \text{D}^{1/4} \text{D}^{3/4} \text{D}^{\circ}$ c $\text{D}^{\circ} \text{D}^{3/4} \text{D}' \text{D}^{3/4} \text{D}^{1/4}$ ABUS 145/30 ($\text{D} - \text{D}_{\mu} \text{D} \gg \tilde{\text{N}}, \tilde{\text{N}} \langle \text{D}^1 \rangle$)		16.10 €









